


el-eCTAL

Nieka® ELECTRIC

Paramount reliability now available for electric fusion



See-through automatic door

Real circular stirring motion
for faster sample dissolution

Clip-on heating modules
for instant maintenance

Very large and
intuitive interface

Powerful fan units for rapid
cold-to-cold operation

USB and network for upgrades
and backups



- fully automated glass bead or solution preparation
- unique safe to touch glass surface
- no fragile ceramic parts
- up to 1250°C fusion temperature
- ultra-precise temperature control for complex pre-oxidation
- exhaust fumes concentrated in a small extraction area
- plug and use in seconds
- 208-240 V / 20 A / 2500W max.